

Product Features

- High-efficiency isobaric filling machine, efficiency improvement>40%, reducing 30%-50% of aging time, reduction of high temperature aging time, and reduction of the volume of secondary filling
- The equipment is mainly used for the filling of prismatic cell, which can realize automatic code scanning, weighing before and after filling, Hi-pot test, isobaric filling (quantitative/variable), wiping, nail insertion etc.

Product Parameters

Capacity	MAX:45PPM
Filling accuracy	≤ ±0.6% (maximum filling volume 1400g)
Filling volume CMK	≥1.67
Filling method	Isobaric filling
Qualification rate	≥99.8%
Utilization rate	≥98%
Positive pressure	0-1.5MPa
Vacuum pressure	≤-95Kpa
Weighing system accuracy	± 0.1g